



# Anchor, PISA Nut, 5/8in threads, Tripleye

By CHANCE Utility  
Catalog # [12593](#)



Tripleye eyenut for 0.625" (15.9 mm) Pisa Rod.

\*Representative Image

## Features

- For use with Pisa style anchor rods
- Eyes are dropped forged for better strength and reliability
- Hot dipped galvanized per ASTM A153
- Not for use on 5/8" Machine Bolts

## Application

Helical Anchoring

## General

Coating	Galvanized, ASTM A-153
Eyenut Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	16000 lb.
Type	Power Installed Screw Anchor (PISA)
UPC	096359068433

## Dimensions

Rod Diameter	0.625 in
Weight	2.313 lb

## Logistics

Pallet Quantity	960
Standard Package	25

## Product Assets

- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06131E\\_PISA\\_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - Nut, Tripleye \(SA12593\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Tough One and PISA Anchor Installation \(VI0645E\)](#)
- [Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

## Related Products

- [12332P - Anchor, PISA Rod, 5/8in X 7ft, 5/8in threads](#)
- [12336P - Anchor, PISA Rod, 5/8in X 3.5ft, 5/8in threads](#)
- [C2030148 - Tripleye® ANCHOR ROD BONDING CLAMP for 5/8in, 3/4in & 1in PISA RODS](#)



A proud member of the Hubbell Family.