



Anchor, PISA Rod, 3/4in X 3.5ft, 1in threads

By CHANCE Utility
Catalog # [12634P](#)

Pisa anchor rod 0.75" (19.1 mm) diameter, 3' 6" (1067 mm) long.



*Representative Image

Features

- Hot forged hex collar provides strong connection to anchor and eye
- Hot dipped galvanized per ASTM A153
- Rods used with PISA® Power Installed Screw Anchors
- Cannot be used with Expanding and Plate Anchors

Application

Helical Anchoring

General

Coating	Galvanized, ASTM A-153
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	23000 lb.
Type	Power Installed Screw Anchor (PISA)
UPC	096359068457

Dimensions

Length	42.000 in
Rod Diameter	0.750 in
Weight	5.880 lb

Logistics

Pallet Quantity	50
Standard Package	5

Product Assets

- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06131E_PISA_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - Anchor Rod, Power Screw \(SA1020001\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Tough One and PISA Anchor Installation \(VI0645E\)](#)
- [Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

Related Products

- [12585 - Anchor, PISA Nut 1in threads Tripleye](#)
- [6512 - Anchor, PISA Nut 1in threads Thimbleye](#)
- [6562 - Anchor, PISA Nut 1in threads Twineye](#)



A proud member of the Hubbell Family.