



## Anchor, Extension, SS5, 14 X 5ft

By Chance  
Catalog # [12656N](#)

Square Shaft (SS 5) Extension 5' long (1524 mm) with 14" (355 mm) Helix



### Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque
- Bolt and nut are assembled to extension at the factory

### General

Application	Helical Anchoring
Catalog Number	12656N
Coating	Galvanized, ASTM A-153
Number of Helices	1
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.
Torque Rating	5500 ft-lbs
Type	Anchor Extensions
UPC	096359068648

### Dimensions

Anchor Helix Diameter(s)	14 in
Dimensions	60.000 in x 14.000 in x 14.000 in
Height	14 in
Length	60 in
Weight	54.88 lb
Width	14 in

### Logistics

Pallet Quantity	12
Standard Package	1

### Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - TD06132E\\_Type\\_SS\\_and\\_RR\\_Anchors](#)
- [Installation Manuals - Chance Helical Pile/Anchor Installation Log Form to record installation details of Chance helical piles.](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance Literature - Anchoring](#)
- [Literature - New Construction Helical Pile Foundation System](#)
- [Sales Drawings - Helical Extension](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process](#)
- [Video - CHANCE Square Shaft Anchor Installation](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-12656N-SPEC-EN | REV 6/2024