



Anchor, Extension, SS5, X 7ft

By CHANCE Utility
Catalog # 12657

Square Shaft (SS 5) Extension 7' long (2134 mm)



*Representative Image

Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque
- Bolt and nut are assembled to extension at the factory

Application

Helical Anchoring

General

Coating	Galvanized, ASTM A-153
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.
Torque Rating	5500 ft-lbs
Type	Anchor Extensions
UPC	096359068655

Dimensions

Length	84.000 in
Weight	55.370 lb

Certifications and Compliance

RUS Listed Reference	z - Anchors, Power-installed screw
----------------------	------------------------------------

Logistics

Pallet Quantity	40
Standard Package	1

Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - SS5 Anchors \(SA11010000\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

Related Products

- [P0010041P - Square Shaft \(SS5/SS150\) Hardware](#)
- [O55449P - Square Shaft \(SS5/SS150\) Nut](#)



A proud member of the Hubbell Family.