



# Anchor, Extension, SS5, X 10ft

By Chance  
Catalog # [12658](#)

Square Shaft (SS 5) Extension 10' long (3048 mm).



## Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque
- Bolt and nut are assembled to extension at the factory

## General

Application	Helical Anchoring
Catalog Number	12658
Coating	Galvanized, ASTM A-153
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.
Torque Rating	5500 ft-lbs
Type	Anchor Extensions
UPC	096359068662

## Dimensions

Dimensions	120.000 in x 3.625 in x 2.500 in
Height	2.5 in
Length	120 in
Weight	76.44 lb
Width	3.625 in

## Certifications And Compliance

RUS Listed Reference	z - Anchors, Power-installed screw
----------------------	------------------------------------

## Logistics

Pallet Quantity	30
Standard Package	1

## Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - TD06132E\\_Type\\_SS\\_and\\_RR\\_Anchors](#)
- [Installation Manuals - Chance Helical Pile/Anchor Installation Log Form to record installation details of Chance helical piles.](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance Literature - Anchoring](#)
- [Literature - New Construction Helical Pile Foundation System](#)
- [Sales Drawings - SS5 Anchors](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process](#)
- [Video - CHANCE Square Shaft Anchor Installation](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-12658-SPEC-EN | REV 6/2024