



Round Rod Extension, 7ft long

By CHANCE Utility
Catalog # 12698

Round Rod Extension, 7' (2134 mm) long.



Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation
- Bolt and nut are assembled to extension at the factory

Application

Helical Anchoring

General

Coating	Galvanized
EU RoHS Indicator	No
Finish Type	Galvanized
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.
Torque Rating	2300 ft-lbs
Type	Round Rod Anchors
UPC	096359068723

Dimensions

Dimensions	84.000 in x 3.500 in x 2.500 in
Height	2.500 in
Length	84.000 in
Weight	33.790 lb
Width	3.500 in

Logistics

Pallet Quantity	30
Standard Package	1

Product Assets

- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - R.R Extension Rod \(SA012696\)](#)
- [Sales Drawings - Rock Anchor Assembly \(SA1040004\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

Related Products

- [P0010041P - Square Shaft \(SS5/SS150\) Hardware](#)
- [O55449P - Square Shaft \(SS5/SS150\) Nut](#)



A proud member of the Hubbell Family.