



ADJUST-A-GRIP GUY DEADEND, 1/2in DIA. STRAND, 26,900lbs STRENGTH

By Chance
Catalog # [12GA18](#)

The Adjust-a-Grip is a deadend for 1/2" dia. 7 or 19 wire galvanized steel guy strand per ASTM A475. Strength exceeds the rated breaking strength of the strand. The U-bolt provides 18" of tension adjustability.

Features

- Quick and easy to install, no special tools or crimping dies required
- Over 40 years proven field reliability

General

Catalog Number	12GA18
EU RoHS Indicator	No
Tensile Strength	26900 lb.
UPC	096359067009

Dimensions

Dimensions	29.375 in x 5.000 in x 3.375 in
Distance From Pole	N/A
Height	3.375 in
Length	29.375 in
Weight	11.03 lb



Width	5 in
-------	------

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Carton Quantity	4
Pallet Quantity	144

Product Assets

- [Catalogs - Adjust-A-Grip Deadend Grips](#)
- [Installation Manuals - Adjust-A-Grip Installation Instructions](#)
- [Literature - Adjust A Grip Guy Deadends](#)
- [Sales Drawings - Adjust-A-Grip, 18" Adjust](#)
- [Specifications - 12GA18](#)
- [Video - CHANCE Adjust a Grip](#)