



# BOLT, DA OVALEYE, 5/8in x 22in

By Chance  
Catalog # [19792](#)



Double-arming eye bolts include an integral eye for the attachment of deadend insulators in double arm applications.

## Features

- 19" thread length
- Includes three square nuts
- Eye dimensions are 5/8" x 1 1/2" x 2"
- Rated tensile strength is 13,550 lbs.
- Galvanized steel per ASTM A-153
- Manufactured in compliance with ANSI C135.4
- RUS listed dy - Bolt, eye, double arming

## General

Catalog Number	19792
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Material	Steel
Tensile Strength	12400 lb.
UPC	096359069010

## Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Distance From Pole	N/A
Length	22 in
Length - Threaded Area	19 in
Weight	2.35 lb

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
RUS Listed Reference	dy - Bolt, eye, double arming

## Logistics

Pallet Quantity	480
-----------------	-----

## Product Assets

- [Catalogs - Communications Catalog](#)
- [Sales Drawings - Bolt, 5/8 Ovaleye Double-Arming](#)
- [Specifications - 19792](#)



A Hubbell brand