



## 0° Communication Standoff Bracket, 24"

By CHANCE Utility  
Catalog # [1CSM240](#)

24" Medium Duty Fiberglass 0° Communication Standoff Bracket



\*Representative Image

### General

Description - End Fitting	Communication clamp
Strength Rating - Minimum Ultimate, Longitudinal (L)	500 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1,500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359592099

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	24.00 in
Length	24.00 in
Mounting Bolt Spacing	6.00 in - 8.00 in
Radius - FWDE Wrap-Around	1.5
Weight	5.4 lb

### Electrical Ratings

Phase	1-Phase
-------	---------

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-32\)](#)

[Catalogs - Communications Catalog \(CA12042E\)](#)

[Sales Drawings - SA-1CSM120](#)

[Video - Hubbell | CHANCE® Communication Stand Off Bracket \(CENT\\_CN\\_VI\\_EN\\_00085\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-1CSM240-SPEC-EN | REV 1/2024