



15° Communication Standoff Bracket, 36"

By Chance
Catalog # 1CSM36

36" Medium Duty Fiberglass 15° Communication Standoff Bracket

Features

- End fitting designed for communication applications
- 1.5" (medium duty) fiberglass rod
- 15° Angle
- Base and end fittings are aluminum alloy

General

Catalog Number	1CSM36
Description - End Fitting	Communication clamp
Strength Rating - Minimum Ultimate, Longitudinal (L)	500 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359268697

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	36 in
Length	36 in



Mounting Bolt Spacing	<ul style="list-style-type: none">• 6 in• 8 in
Weight	6.8 lb

Electrical Ratings

Phase	1-Phase
-------	---------

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	-----------------------------------------------------

Logistics

Pallet Quantity	50
Standard Package	1

Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products](#)
- [Catalogs - Communications Catalog](#)
- [Sales Drawings - Standoff, Communications](#)
- [Specifications - 1CSM36](#)
- [Video - Hubbell | CHANCE® Communication Stand Off Bracket](#)



A Hubbell brand