

Vertical Pin Standoff Bracket, 12"

By Chance

Catalog # [1SBH12V2](#)

Bracket, 12" Heavy Duty Single-Phase Vertical Pin Standoff



*Representative Image

Features

- Pin Type Insulator
- 1" Nylon Threads

General

Catalog Number	1SBH12V2
Description - End Fitting	Vertical Pin
Material - Threads	1" Injection Molded Nylon Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	2000 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2550 lb
UPC	096359825661

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	12 in
Length	12 in
Mounting Bolt Spacing	8 in
	10 in
Weight	10 lb

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)

[Literature - Nylon Pin Bracket](#)

[Sales Drawings - 2" Vertical Pin Standoff Bracket](#)