



15° 7-Hole Dual Function Cloverleaf Cutout / Arrester Standoff Bracket, 18" (No Hardware)

By CHANCE Utility
Catalog # [1SBH18CL](#)



18" Heavy Duty Fiberglass 15° 7-Hole Dual Function Cloverleaf Cutout / Arrester Standoff Bracket (No Hardware)

*Representative Image

Features

- Not recommended for use with TripSaver® Reclosers

General

Description - End Fitting	3 Position Cloverleaf Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	1400 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2250 lb
UPC	096359235873

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	18 in
Length	18.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 8.00 in• 10.00 in
Weight	7.5 lb

Electrical Ratings

Phase	1-Phase
-------	---------

Logistics

Pallet Quantity	96
Standard Package	4

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-48\)](#)
[Catalogs - CHANCE® Fiberglass Construction Products \(Catalog 12\)](#)
[Sales Drawings - Single Phase_3 Position_HD Cloverleaf Standoff bracket](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-1SBH18CL-SPEC-EN | REV 7/2023