



Vertical Pin Standoff Bracket,18" w/ Nylon

By CHANCE Utility
Catalog # 1SBH18V2

Bracket, 18" Heavy Duty Single-Phase Vertical Pin Standoff



*Representative Image

Features

- Not recommended for use with TripSaver® Reclosers

General

Description - End Fitting	Vertical Pin
Material - Threads	1" Injection Molded Nylon Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1950 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2250 lb
UPC	096359565611

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	18 in
Length	18.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 8.00 in• 10.00 in
Weight	11.30 lb

Logistics

Standard Package	1
------------------	---

Product Assets

- Catalog Page - CHANCE® Fiberglass Construction Products (Page 12-24)
- Catalogs - CHANCE® Fiberglass Construction Products (Catalog 12)
- Literature - Nylon Pin Bracket (SF09039E)
- Sales Drawings - 2" Vertical Pin Standoff Bracket (SA_1SBH12V1)



A proud member of the Hubbell Family.