



## Horizontal Pin Standoff Bracket, 23"

By CHANCE Utility  
Catalog # [1SBH23H4](#)

23" Heavy Duty Fiberglass Single-Phase Horizontal Pin Standoff Bracket with 1.375" Lead Threads



\*Representative Image

### Features

- Not recommended for use with TripSaver® Reclosers

### General

Description - End Fitting	Horizontal Pin
Material - Threads	1.375" Lead Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1240 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1860 lb

### Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	23 in
Length	23.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 8.00 in</li><li>• 10.00 in</li></ul>
Weight	9.6 lb

### Logistics

Standard Package	2
------------------	---

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-25\)](#)



A proud member of the Hubbell Family.