



15° 2-Position Cutout / Arrester Standoff Bracket (No Hardware), 24"

By Chance

Catalog # [1SBH24AMT](#)

24" Heavy Duty Fiberglass 15° 2-Position Cutout / Arrester Standoff Bracket (No Hardware)



*Representative Image

Features

Not recommended for use with TripSaver® Reclosers

General

Catalog Number	1SBH24AMT
Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	1100 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1900 lb
UPC	096359408093

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	24 in
Length	24 in
Mounting Bolt Spacing	8 in
	10 in
Weight	10.4 lb

Electrical Ratings

Phase	1-Phase
-------	---------

Logistics

Standard Package	4
------------------	---

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)