



# 15° 2-Position Cutout / Arrester Standoff Bracket (No Hardware), 24"

By Chance  
Catalog # 1SBH24AMT



\*Representative Image

24" Heavy Duty Fiberglass 15° 2-Position Cutout / Arrester Standoff Bracket (No Hardware)

### Features

- Two position ("T" bracket) end fitting
- 2" (heavy duty) fiberglass rod
- 15° angle
- Base is hot dip galvanized ductile iron, end fitting is aluminum alloy

### General

Catalog Number	1SBH24AMT
Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	1100 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1900 lb
UPC	096359408093

### Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	24 in
Length	24 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 8 in</li><li>• 10 in</li></ul>
Weight	10.4 lb

### Electrical Ratings

Phase	1-Phase
-------	---------

### Logistics

Standard Package	4
------------------	---

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products Specifications - 1SBH24AMT](#)