



## Horizontal Pin Standoff Bracket, 24"

By CHANCE Utility  
Catalog # [1SBH24H2](#)

24" Heavy Duty Fiberglass Single-Phase Horizontal Pin  
Standoff Bracket with 1" Nylon Threads



\*Representative Image

### Features

- Not recommended for use with TripSaver® Reclosers

### General

|   |                  |
|---|------------------|
| Description - End Fitting                               | Horizontal Pin   |
| Material - Threads                                      | 1" Nylon Threads |
| Strength Rating - Minimum<br>Ultimate, Longitudinal (L) | 1200 lb          |
| Strength Rating - Minimum<br>Ultimate, Transverse (T)   | 1500 lb          |
| Strength Rating - Minimum<br>Ultimate, Vertical (V)     | 1750 lb          |
| UPC   | 096359588078     |

### Dimensions

|                       |  |
|-----------------------|--|
| Diameter - Rod / Tube | 2 in   |
| Distance From Pole    | 24 in  |
| Length                | 24.00 in   |
| Mounting Bolt Spacing | <ul style="list-style-type: none"><li>• 8.00 in</li><li>• 10.00 in</li></ul> |
| Weight                | 9.8 lb   |

### Logistics

|                  |   |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-25\)](#)  
[Sales Drawings - SA1SBHXXHX](#)



A proud member of the Hubbell Family.