



# Horizontal Line Post Insulator Standoff Bracket, 24"

By Chance  
Catalog # [1SBH24PF](#)



\*Representative Image

## Features

- Horizontal Post Insulator Bracket
- 2" (heavy duty) fiberglass rod
- 15° Angle
- Base and end fittings are hot dip galvanized ductile iron

## General

Catalog Number	1SBH24PF
Description - End Fitting	Post Insulator
Strength Rating - Minimum Ultimate, Longitudinal (L)	1200 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1450 lb
UPC	096359533085

## Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	24 in
Length	24 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 8 in</li><li>• 10 in</li></ul>
Weight	15.2 lb

## Electrical Ratings

Phase	1-Phase
-------	---------

## Logistics

Standard Package	1
------------------	---

## Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)  
[Specifications - 1SBH24PF](#)



A Hubbell brand