



Vertical Pin Standoff Bracket, 24"

By CHANCE Utility
Catalog # [1SBH24V1](#)

24" Heavy Duty Fiberglass Single-Phase Vertical Pin Standoff Bracket with 1" Plasticol Coated Threads



*Representative Image

Features

- Not recommended for use with TripSaver® Reclosers

General

Description - End Fitting	Vertical Pin
Material - Threads	1" Plastisol Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1850 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2100 lb
UPC	096359067344

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	24 in
Length	24.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 8.00 in• 10.00 in
Weight	12.7 lb

Logistics

Pallet Quantity	48
Standard Package	2

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-24\)](#)

[Sales Drawings - 2" Vertical Pin Standoff Bracket \(SA_1SBH12V1\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-1SBH24V1-SPEC-EN | REV 1/2024