



Horizontal Pin Standoff Bracket, 27"

By CHANCE Utility
Catalog # [1SBH27H2](#)

27" Heavy Duty Fiberglass Single-Phase Horizontal Pin Standoff Bracket with 1" Nylon Threads



*Representative Image

Features

- Not recommended for use with TripSaver® Reclosers

General

Description - End Fitting	Horizontal Pin
Material - Threads	1" Nylon Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1050 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1550 lb

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	27 in
Length	27.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 8.00 in• 10.00 in
Weight	10.4 lb

Logistics

Carton Quantity	2
Standard Package	1

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-25\)](#)
[Sales Drawings - SA1SBHXXHX](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-1SBH27H2-SPEC-EN | REV 1/2024