

## Vertical Pin Standoff Bracket, 27"

By Chance  
Catalog # [1SBH27V2](#)

27" Heavy Duty Fiberglass Single-Phase Vertical Pin Standoff Bracket with 1" Nylon Threads



\*Representative Image

### Features

- Pin Type Insulator
- 1" Nylon Threads

### General

Catalog Number	1SBH27V2
Description - End Fitting	Vertical Pin
Material - Threads	1" Nylon Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1950 lb
UPC	096359639787

### Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	27 in
Length	27 in
Mounting Bolt Spacing	8 in
	10 in
Weight	13.4 lb

### Logistics

Standard Package	1
------------------	---

### Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products](#)
- [Literature - Nylon Pin Bracket](#)
- [Sales Drawings - 2" Vertical Pin Standoff Bracket](#)