

## Vertical Pin Standoff Bracket, 27"

By Chance  
Catalog # [1SBH27V4](#)

27" Heavy Duty Fiberglass Single-Phase Vertical Pin Standoff Bracket with 1.375" Lead Threads



\*Representative Image

### Features

- Pin Type Insulator
- 1.375" Lead Threads

### General

|  |                     |
|--|---------------------|
| Catalog Number                                       | 1SBH27V4            |
| Description - End Fitting                            | Vertical Pin        |
| Material - Threads                                   | 1.375" Lead Threads |
| Strength Rating - Minimum Ultimate, Longitudinal (L) | 1800 lb             |
| Strength Rating - Minimum Ultimate, Transverse (T)   | 2500 lb             |
| Strength Rating - Minimum Ultimate, Vertical (V)     | 1950 lb             |
| UPC  | 096359359920        |

### Dimensions

|                       |         |
|-----------------------|---------|
| Diameter - Rod / Tube | 2 in    |
| Distance From Pole    | 27 in   |
| Length                | 27 in   |
| Mounting Bolt Spacing | 8 in    |
|                       | 10 in   |
| Weight                | 13.4 lb |

### Logistics

|                  |   |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)  
[Sales Drawings - 2" Vertical Pin Standoff Bracket](#)