



## Horizontal Pin Standoff Bracket, 30"

By CHANCE Utility  
Catalog # [1SBH30H4](#)

30" Heavy Duty Fiberglass Single-Phase Horizontal Pin Standoff Bracket with 1.375" Lead Threads



\*Representative Image

### Features

- Not recommended for use with TripSaver® Reclosers

### General

Description - End Fitting	Horizontal Pin
Material - Threads	1.375" Lead Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	950 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1400 lb
UPC	096359067429

### Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	30 in
Length	30.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 8.00 in</li><li>• 10.00 in</li></ul>
Weight	11.1 lb

### Logistics

Pallet Quantity	40
Standard Package	1

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-25\)](#)  
[Sales Drawings - SA1SBHXXHX](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-1SBH30H4-SPEC-EN | REV 1/2024