



## 15° 2-Position Cutout / Arrester Standoff Bracket w/ Hardware, 12"

By CHANCE Utility  
Catalog # [1SBM12AMTB](#)

12" Medium Duty Fiberglass 15° 2-Position Cutout / Arrester Standoff Bracket w/ Hardware



\*Representative Image

### Features

- Not recommended for use with TripSaver® Reclosers

### General

Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	1400 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1800 lb
UPC	096359396338

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	12 in
Length	12.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 6.00 in</li><li>• 8.00 in</li></ul>
Weight	6.6 lb

### Electrical Ratings

Phase	1-Phase
-------	---------

### Logistics

Carton Quantity	5
Pallet Quantity	120
Standard Package	1

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-45\)](#)  
[Sales Drawings - Standoff, Single Phase, 15° "T" End Ferrule \(SA1SBM12AMT\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-1SBM12AMTB-SPEC-EN | REV 1/2024