



15° 4-Hole 3-Position Cloverleaf Cutout / Arrester Standoff Bracket w/ Hardware, 12"

By Chance

Catalog # [1SBM12CLH](#)



12" Medium Duty Fiberglass 15° 4-Hole 3-Position Cloverleaf Cutout / Arrester Standoff Bracket w/ Hardware

*Representative Image

Features

Not recommended for use with TripSaver® Reclosers

General

Catalog Number	1SBM12CLH
Description - End Fitting	3 Position Cloverleaf Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	1400 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1800 lb
UPC	096359359869

Dimensions

Diameter - Rod / Tube	1.5 in
Dimensions	12.00 in x 2.6 in x 2 in
Distance From Pole	12 in
Height	2 in
Length	12 in
Mounting Bolt Spacing	6 in
	8 in
Weight	7.71 lb
Width	2.6 in

Electrical Ratings

Phase	1-Phase
-------	---------

Logistics

Carton Quantity	5
Pallet Quantity	120
Standard Package	5

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)
[Catalogs - CHANCE® Fiberglass Construction Products](#)
[Sales Drawings - 4-Hole Cloverleaf Single Phase \(15°\)](#)



A Hubbell brand