



Horizontal Pin Standoff Bracket, 12"

By CHANCE Utility
Catalog # [1SBM12H3](#)

12" Medium Duty Fiberglass Single-Phase Horizontal Pin
Standoff Bracket with 1" Lead Threads



*Representative Image

Features

- Not recommended for use with TripSaver® Reclosers

General

Description - End Fitting	Horizontal Pin
Material - Threads	1" Lead Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1850 lb
UPC	096359067481

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	12 in
Length	12.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 6.00 in• 8.00 in
Weight	5.2 lb

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-25\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-1SBM12H3-SPEC-EN | REV 1/2024