



# Horizontal Pin Standoff Bracket, 14"

By Chance  
Catalog # 1SBM14H4

14" Medium Duty Fiberglass Single-Phase Horizontal Pin Standoff Bracket with 1.375" Lead Threads



\*Representative Image

## Features

- Horizontal Position Pin Type Insulator Bracket
- 1.5" (medium duty) fiberglass rod
- 15° Angle
- Base and end fittings are hot dip galvanized ductile iron

## General

Catalog Number	1SBM14H4
Description - End Fitting	Horizontal Pin
Material - Threads	Lead
Strength Rating - Minimum Ultimate, Longitudinal (L)	1600 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1600 lb
UPC	096359067580

## Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	14 in
Length	14 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 6 in</li><li>• 8 in</li></ul>
Weight	5.5 lb

## Electrical Ratings

Phase	1-Phase
-------	---------

## Logistics

Pallet Quantity	144
Standard Package	6

## Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products Specifications - 1SBM14H4](#)