



15° 2-Position Cutout / Arrester Standoff Bracket w/ Hardware & Spacer Bar, 15"

By Chance
Catalog # 1SBM15AMSB

15" Medium Duty Fiberglass 15° 2-Position Single-Phase Cutout / Arrester Bracket w/ Hardware & Spacer Bar

Features

- Single position end fitting with spacer bar
- 1.5" (medium duty) fiberglass rod
- 15° angle
- Base is hot dip galvanized ductile iron, end fitting is aluminum alloy

General

Catalog Number	1SBM15AMSB
Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	1100 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1500 lb
UPC	096359574200

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	15 in
Length	15 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 6 in• 8 in
Weight	6.6 lb

Electrical Ratings

Phase	1-Phase
-------	---------

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products Specifications - 1SBM15AMSB](#)



A Hubbell brand