



## Suspension Standoff Bracket, 15"

By CHANCE Utility  
Catalog # [1SBM15S](#)

15" Medium Duty Single-Phase Fiberglass Suspension Standoff Bracket



### Features

- Not recommended for use with TripSaver® Reclosers

### General

Description - End Fitting	Suspension
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1500 lb
UPC	096359360247

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	15 in
Length	15.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 6.00 in</li><li>• 8.00 in</li></ul>
Weight	5.6 lb

### Logistics

Carton Quantity	6
Standard Package	1

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-34\)](#)  
[Sales Drawings - SA1SBMXXS](#)



A proud member of the Hubbell Family.