



## Vertical Pin Standoff Bracket, 16"

By CHANCE Utility  
Catalog # [1SBM16V4](#)

16" Medium Duty Fiberglass Single-Phase Vertical Pin Standoff Bracket with 1.375" Lead Threads



\*Representative Image

### Features

- Not recommended for use with TripSaver® Reclosers

### General

Description - End Fitting	Vertical Pin
Material - Threads	1.375" Lead Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1000 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1600 lb
UPC	096359067719

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	16 in
Length	16.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 6.00 in</li><li>• 8.00 in</li></ul>
Weight	7.3 lb

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-24\)](#)



A proud member of the Hubbell Family.