



## 15° 4-Hole 3-Position Cloverleaf Cutout / Arrester Standoff Bracket w/ Hardware, 18"

By CHANCE Utility  
Catalog # 1SBM18CLH



18" Medium Duty Fiberglass 15° 4-Hole 3-Position Cloverleaf Cutout / Arrester Standoff Bracket w/ Hardware

\*Representative Image

### Features

- Not recommended for use with TripSaver® Reclosers

### General

Description - End Fitting	3 Position Cloverleaf Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	950 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359067740

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	18 in
Length	18.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 6.00 in</li><li>• 8.00 in</li></ul>
Weight	7.4 lb

### Electrical Ratings

Phase	1-Phase
-------	---------

### Logistics

Pallet Quantity	80
Standard Package	5

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-47\)](#)  
[Catalogs - CHANCE® Fiberglass Construction Products \(Catalog 12\)](#)  
[Sales Drawings - 4-Hole Cloverleaf Single Phase \(15°\) \(SA1SBM12CL\)](#)  
[Video - HUBBELL® CHANCE® Stainless Steel Banding \(VIO6080E\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-1SBM18CLH-SPEC-EN | REV 7/2023