



## 5° 2-Position Cutout / Arrester Standoff Bracket w/ Hardware & Spacer Bar, 18"

By CHANCE Utility  
Catalog # [1SBM18CSB](#)



18" Medium Duty Fiberglass 5° 2-Position Cutout / Arrester Standoff Bracket w/ Hardware & Spacer Bar

\*Representative Image

### Features

- Not recommended for use with TripSaver® Reclosers

### General

Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	700 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1500 lb
UPC	096359231813

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	18 in
Length	18.00 in
Mounting Bolt Spacing	8.00 in
Weight	4.4 lb

### Electrical Ratings

Phase	1-Phase
-------	---------

### Logistics

Pallet Quantity	180
Standard Package	6

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-43\)](#)  
[Sales Drawings - SA1SBMXXCB](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-1SBM18CSB-SPEC-EN | REV 1/2024