



15° Tear Drop Cutout / Arrester Standoff Bracket w/ Hardware, 18"

By Chance
Catalog # 1SBM18TDB



15° Tear Drop Cutout / Arrester Standoff Bracket, 18"

Features

- Single position tear drop end fitting with hardware (bolt, nut, and washers)
- 1.5" (medium duty) fiberglass rod
- 15° angle
- Base and end fittings are hot dip galvanized ductile iron

General

Catalog Number	1SBM18TDB
Description - End Fitting	Tear Drop
Strength Rating - Minimum Ultimate, Longitudinal (L)	900 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359597261

Dimensions

Diameter - Rod / Tube	1.5 in
Dimensions	18 in x 3 in x 12.75 in
Distance From Pole	18 in
Height	12.75 in
Length	18 in

Mounting Bolt Spacing	<ul style="list-style-type: none">• 6 in• 8 in
Radius - FWDE Wrap-Around	1.5
Weight	9 lb
Width	3 in

Electrical Ratings

Phase	1-Phase
-------	---------

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	80
Standard Package	5

Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products](#)
- [Catalogs - CHANCE® Fiberglass Construction Products](#)
- [Sales Drawings - Single Phase_Tear Drop Standoff bracket with hardware](#)
- [Specifications - 1SBM18TDB](#)



A Hubbell brand