



## Vertical Pin Standoff Bracket, 18" w/ Plastisol

By CHANCE Utility  
Catalog # [1SBM18V1](#)

18" Medium Duty Fiberglass Single-Phase Vertical Pin Standoff Bracket with 1" Plastisol Coated Threads



\*Representative Image

### Features

- Not recommended for use with TripSaver® Reclosers

### General

Description - End Fitting	Vertical Pin
Material - Threads	1" Plastisol Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	950 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359067801

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	18 in
Length	18.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 6.00 in</li><li>• 8.00 in</li></ul>
Weight	7.5 lb

### Logistics

Pallet Quantity	120
Standard Package	6

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-24\)](#)  
[Catalogs - CHANCE® Fiberglass Construction Products \(Catalog 12\)](#)  
[Sales Drawings - 1-1/2" Vertical Pin Standoff \(SA1SBM12V1\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-1SBM18V1-SPEC-EN | REV 7/2023