



0° 1-Position Cutout / Arrester Standoff Bracket w/ Hardware, 21"

By Chance

Catalog # [1SBM21SGLB](#)

21" Medium Duty Fiberglass 0° 1-Position Cutout / Arrester Standoff Bracket w/ Hardware



*Representative Image

Features

Not recommended for use with TripSaver® Reclosers

General

Catalog Number	1SBM21SGLB
Description - End Fitting	1 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	600 lb
Strength Rating - Minimum Ultimate, Transverse (T)	5,000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1,200 lb
UPC	096359616436

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	21 in
Length	21 in
Mounting Bolt Spacing	6 in
	8 in
Weight	5.8 lb

Electrical Ratings

Phase	1-Phase
-------	---------

Logistics

Pallet Quantity	168
Standard Package	6

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)



A Hubbell brand