

Vertical Pin Standoff Bracket, 21"

By Chance
Catalog # [1SBM21V2](#)

21" Medium Duty Fiberglass Single-Phase Vertical Pin Standoff Bracket with 1" Nylon Threads



*Representative Image

Features

- Pin Type Insulator
- 1" Nylon Threads

General

Catalog Number	1SBM21V2
Description - End Fitting	Vertical Pin
Material - Threads	1" Nylon Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359728238

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	21 in
Length	21 in
Mounting Bolt Spacing	6 in
	8 in
Weight	7.9 lb

Logistics

Pallet Quantity	120
Standard Package	1

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)
[Literature - Nylon Pin Bracket](#)