



# 15° Tear Drop Cutout / Arrester Standoff Bracket, 24"

By Chance  
Catalog # 1SBM24TDB



15° Tear Drop Cutout / Arrester Standoff Bracket, 24"

\*Representative Image

## Features

- Single position tear drop end fitting with hardware (bolt, nut, and washers)
- 1.5" (medium duty) fiberglass rod
- 15° angle
- Base and end fittings are hot dip galvanized ductile iron

## General

Catalog Number	1SBM24TDB
Description - End Fitting	Tear Drop
Strength Rating - Minimum Ultimate, Longitudinal (L)	700 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359597261

## Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	24 in
Length	24 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 6 in</li><li>• 8 in</li></ul>
Radius - FWDE Wrap-Around	1.5
Weight	11.2 lb

## Electrical Ratings

Phase	1-Phase
-------	---------

## Logistics

Standard Package	5
------------------	---

## Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)  
[Specifications - 1SBM24TDB](#)



A Hubbell brand