



## Vertical Pin Standoff Bracket, 24"

By Chance

Catalog # [1SBM24V2](#)

24" Medium Duty Fiberglass Single-Phase Vertical Pin Standoff Bracket with 1" Nylon Threads



\*Representative Image

### Features

- Pin Type Insulator
- 1" Nylon Threads

### General

Catalog Number	1SBM24V2
Description - End Fitting	Vertical Pin
Material - Threads	1" Nylon Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	700 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359714637

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	24 in
Length	24 in
Mounting Bolt Spacing	6 in
	8 in
Weight	8.3 lb

### Logistics

Carton Quantity	6
Pallet Quantity	120
Standard Package	1

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)

[Literature - Nylon Pin Bracket](#)

[Sales Drawings - SA1SBMxxV1\\_\\_B](#)



A Hubbell brand