



## Snatch Block with Forged Steel Hook, 1,250 lb.

By CHANCE Utility  
Catalog # [22301](#)

Light-weight cast-aluminum housing and sheave with a hinged cotterlock yoke and forged steel hook makes for quick rigging in diversified applications.



### Features

- Spring Loaded safety latch on forged steel hook
- Sheave operates on bronze oilite bearings
- Maximum rope size is 5/8"
- Maximum rated working load 1,250 lb.
- Replacement Ball Lok pin and chain PS400006 available separately

### General

EU RoHS Indicator	No
Material	Cast Aluminum
Max Load Lbs.	1250 lb
Style	With Steel Hook
Swivel Top?	Yes
Type	Load Lift Assist
UPC	096359069775

### Dimensions

Weight	2.0 lb
WeightMetric	0.91 kg

### Logistics

Pallet Quantity	300
Standard Package	1

### Product Assets

[Catalogs - Load Handling Accessories \(1250\)](#)  
[Installation Manuals - CHANCE Snatch Block 22301 ENG](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-22301-SPEC-EN | REV 7/2023