



Snatch Block with Steel Meat Hook, 1,250 lb. (566 kg) Working Load Limit

By CHANCE Lineman Grade Tools
Catalog # [22302](#)

Light-weight cast-aluminum housing and sheave with a hinged cotterlock yoke and forged steel hook makes for quick rigging in diversified applications.

Features

- Steel Meat hook version
- Sheave operates on bronze oilite bearings
- Maximum rope size is 5/8"
- Maximum rated working load 1,250 lb.
- Replacement Ball Lok pin and chain PS400006 available separately

Dimensions

Weight	2 lb.
WeightMetric	0.9 kg

Force Related

Max Load Lbs.	1250 lb.
---------------	----------

General



Swivel Top?	Yes
Material type	Standard
Product Type	Snatch Block
Style	With Meat Hook
UPC	096359069782
Type	Load Lift Assist
Material	Cast Aluminum

Logistics

Pallet Quantity	300
Carton Quantity	1
Standard Package	1

Product Assets

[Catalog \[English\]](#)