



BOLT, OVALEYE, 1/2in x 12in

By Chance
Catalog # [29943](#)



Ovaleye bolts are used to support suspension insulators in deadend applications.

Features

- 6" thread length
- Includes one square nut
- Eye dimensions are 7/16" x 1 1/4" x 1 1/5/8"
- Rated tensile strength is 7,800 lbs.
- Galvanized steel per ASTM A-153

General

Catalog Number	29943
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Material	Steel
Tensile Strength	7800 lb.
UPC	096359069911

Dimensions

Diameter	0.5 in
Diameter (Fraction)	1/2 in
Dimensions	14.750 in x 1.125 in x 0.750 in

Distance From Pole	N/A
Height	0.75 in
Length	14.75 in
Length - Threaded Area	6 in
Weight	0.98 lb
Width	1.125 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	ANSI C135.5

Logistics

Pallet Quantity	2400
-----------------	------

Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Pole Line Hardware](#)
- [Sales Drawings - 1/2 Oval Eye Bolt](#)
- [Specifications - 29943](#)



A Hubbell brand