



BOLT, OVALEYE, 3/4in x 10in

By CHANCE Utility
Catalog # 29980



Ovaleye bolts are used to support suspension insulators in deadend applications.

*Representative Image

Features

- 4" thread length
- Includes one square nut
- Eye dimensions are 5/8" x 1 1/2" x 2"
- Rated tensile strength is 20,050 lbs.
- Galvanized steel per ASTM A-153
- RUS listed o - Bolt, eye, oval

General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	18350 lb.
UPC	096359070023

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Length	10.00 in
Length - Threaded Area	4.00 in
Weight	2.00 lb

Certifications and Compliance

RUS Listed Reference o - Bolt, eye, oval

Logistics

Pallet Quantity 1200

Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)
[Catalogs - Pole Line Hardware](#)
[Sales Drawings - Oval eye Bolt, 3/4" \(SA29978\)](#)

Related Products

[C2050187 - SPRING WASHER, REGULAR-DUTY DOUBLE-COIL, 3/4in SIZE](#)
[6814 - WASHER, SQ FLAT, 3/4in SIZE, 2 1/4in](#)
[6823 - WASHER, SQ CURVED, 7/8in HOLE, 3in SQ](#)
[3513 - MF TYPE CURVED LOCK NUT, 3/4in THREAD](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-29980-SPEC-EN | REV 7/2023