



15° 2-Position Cutout / Arrester Standoff Bracket, 36" 2-Phase

By Chance
Catalog # 2SBH36AMTAMT



36 Heavy Duty 15° 2-Position Two-Phase Cutout / Arrester Standoff Bracket

*Representative Image

Features

- Two position ("T" bracket) end fitting
- 2" (heavy duty) fiberglass rod
- 15° angle
- Base is hot dip galvanized ductile iron, end fitting is aluminum alloy

General

Catalog Number	2SBH36AMTAMT
Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	1800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2300 lb
UPC	096359701484

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	36 in
Length	36 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 5 in• 6 in• 8 in
Weight	20.2 lb

Electrical Ratings

Phase	2-Phase
-------	---------

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)
[Specifications - 2SBH36AMTAMT](#)



A Hubbell brand