



15° 2-Position Cutout / Arrester Standoff Bracket w/ Hardware, 36" 2-Phase

By Chance

Catalog # 2SBH36AMTBAMTB



36 Heavy Duty 15° 2-Position Two-Phase Cutout / Arrester
Standoff Bracket w/ Hardware

*Representative Image

Features

- 2 position "T" bracket with hardware (captive bolt, nut, and washers)
- 2" (heavy duty) fiberglass rod
- 15° Angle
- Base is hot dip galvanized ductile iron, end fitting is aluminum alloy

General

| | |
|--|----------------------------|
| Catalog Number | 2SBH36AMTBAMTB |
| Description - End Fitting | 2 Position Apparatus Mount |
| Strength Rating - Minimum Ultimate, Longitudinal (L) | 1800 lb |
| Strength Rating - Minimum Ultimate, Transverse (T) | 10000 lb |
| Strength Rating - Minimum Ultimate, Vertical (V) | 2300 lb |
| UPC | 096359823926 |

Dimensions

| | |
|-----------------------|--|
| Diameter - Rod / Tube | 2 in |
| Distance From Pole | 36 in |
| Length | 36 in |
| Mounting Bolt Spacing | <ul style="list-style-type: none">• 5 in• 6 in• 8 in |
| Weight | 20.2 lb |

Electrical Ratings

| Phase | 2-Phase |
|-------|---------|
|-------|---------|

Logistics

| | |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

Product Assets

Catalog Page - CHANCE® Fiberglass Construction Products
Specifications - 2SBH36AMTBAMTB



A Hubbell brand