



15° 7-Hole Dual Function Cloverleaf Cutout / Arrester Standoff Bracket, 36" 2-Phase

By Chance
Catalog # [2SBH36CLCL](#)



36" Heavy Duty Fiberglass 15° 7-Hole Dual Function Cloverleaf
Two-Phase Cutout / Arrester Standoff Bracket

*Representative Image

General

Catalog Number	2SBH36CLCL
Description - End Fitting	3 Position Cloverleaf Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	1900 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2600 lb

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	36 in
Length	36 in
Mounting Bolt Spacing	5 in
	6 in
	8 in
Weight	20.2 lb

Electrical Ratings

Phase	2-Phase
-------	---------

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)
[Sales Drawings - SA2SBH48CLCL](#)