



Horizontal Pin Standoff Bracket, 36" Two-Phase

By CHANCE Utility
Catalog # [2SBH36HH4](#)



36" Heavy Duty Fiberglass Two-Phase Horizontal Pin Standoff Bracket with 1.375" Lead Threads

*Representative Image

General

Description - End Fitting	Horizontal Pin
Material - Threads	1.375" Lead Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	2000 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2550 lb
UPC	096359069058

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	36 in
Length	36.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 5.00 in• 6.00 in• 8.00 in
Weight	14.9 lb

Logistics

Standard Package 1

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-30\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-2SBH36HH4-SPEC-EN | REV 1/2024