



15° 7-Hole Dual Function Cloverleaf Cutout / Arrester Standoff Bracket, 42" 2-Phase

By CHANCE Utility
Catalog # [2SBH42CLCL](#)



42" Heavy Duty Fiberglass 15° 7-Hole Dual Function Cloverleaf Two-Phase Cutout / Arrester Standoff Bracket

*Representative Image

General

| | |
|--|---------------------------------------|
| Description - End Fitting | 3 Position Cloverleaf Apparatus Mount |
| Strength Rating - Minimum Ultimate, Longitudinal (L) | 1900 lb |
| Strength Rating - Minimum Ultimate, Transverse (T) | 10000 lb |
| Strength Rating - Minimum Ultimate, Vertical (V) | 2400 lb |

Dimensions

| | |
|-----------------------|---|
| Diameter - Rod / Tube | 2 in |
| Distance From Pole | 42 in |
| Length | 42.00 in |
| Mounting Bolt Spacing | <ul style="list-style-type: none">• 5.00 in• 6.00 in• 8.00 in |
| Weight | 21.3 lb |

Electrical Ratings

| | |
|-------|---------|
| Phase | 2-Phase |
|-------|---------|

Logistics

| | |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-51\)](#)
[Sales Drawings - SA2SBH48CLCL](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-2SBH42CLCL-SPEC-EN | REV 1/2024