



Vertical Pin Standoff Bracket, 42" Two-Phase

By CHANCE Utility
Catalog # [2SBH42VV3](#)

42" Heavy Duty Fiberglass Two-Phase Vertical Pin Standoff
Bracket with 1" Lead Threads



*Representative Image

General

Description - End Fitting	Vertical Pin
Material - Threads	1" Lead Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1700 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2400 lb
UPC	096359069133

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	42 in
Length	42.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 5.00 in• 6.00 in• 8.00 in
Weight	22.1 lb

Logistics

Pallet Quantity	24
Standard Package	1

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-29\)](#)



A proud member of the Hubbell Family.