



# Horizontal Pin Standoff Bracket, 48" Two-Phase

By Chance  
Catalog # [2SBH48HH3](#)



48" Heavy Duty Fiberglass Two-Phase Horizontal Pin Standoff Bracket with 1" Lead Threads

\*Representative Image

### Features

- Horizontal Position Pin Type Insulator Bracket
- 2" (heavy duty) fiberglass rod
- 15° Angle
- Base and end fittings are hot dip galvanized ductile iron

### General

Catalog Number	2SBH48HH3
Description - End Fitting	Horizontal Pin
Material - Threads	Lead
Strength Rating - Minimum Ultimate, Longitudinal (L)	1900 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2250 lb
UPC	096359069164

### Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	48 in
Length	48 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 5 in</li><li>• 6 in</li><li>• 8 in</li></ul>
Weight	17.6 lb

### Electrical Ratings

Phase	2-Phase
-------	---------

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products Specifications - 2SBH48HH3](#)