



Vertical Pin Standoff Bracket, 30" Two-Phase

By CHANCE Utility
Catalog # [2SBM30VV2](#)



*Representative Image

30" Medium Duty Fiberglass Two-Phase Vertical Pin Standoff Bracket with 1" Nylon Threads

General

Description - End Fitting	Vertical Pin
Material - Threads	1" Nylon Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1100 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1800 lb

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	30 in
Length	30.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 5.00 in• 6.00 in• 8.00 in
Weight	12.3 lb

Logistics

Standard Package 1

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-29\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-2SBM30VV2-SPEC-EN | REV 1/2024